


# Valena™ Life

## Connected Wake up/Sleep wireless control

Cat. Nos: 7 521 89 - 7 522 89 - 7 523 89



### 1. USE


Used to control wake up/sleep scenes involving lights, roller shutters and connected sockets.

- Fixes directly on the wall or screws onto a flush-mounting box.
- Multi-gang versions can be combined with other wiring accessories.
- Fits on a piece of furniture (movable).

### 2. RANGE


Description	White	Ivory	Aluminium
Wake up/Sleep wireless control, with battery. Supplied complete. Equipped with an LED indicator (configuration) and a RESET button (hidden) used to return to factory settings. Repositionable self-adhesive fixings supplied.	7 521 89	7 522 89	7 523 89

### 3. DIMENSIONS



A	B	C
86	86	12

### 4. OPERATION



### 5. TECHNICAL CHARACTERISTICS

#### ■ 5.1 Mechanical characteristics

Protection against impacts: IK 02  
 Protection against solid bodies/liquids:  
 - IP 20 without plate and rocker plate  
 - IP 40 for assembled product

#### ■ 5.2 Material characteristics

Plate: ABS - Sub-plate: PC  
 Rocker plate: ABS  
 Colours: White RAL 9003 - Ivory: RAL 1013  
 Aluminium  
 Mechanism with grid: Fibreglass-reinforced (10 %) PC  
 Halogen-free  
 UV resistant

Self-extinguishing: 650°C/30 s

#### ■ 5.3 Electrical characteristics

Powered by a CR2032 - 3 V lithium battery (supplied)  
 Battery life: 8 years for 10 activations a day  
**ZigBee radio technology** frequency: 2.4 GHz to 2.4835 GHz  
 Wireless mesh network, self-adaptive and secure (AES 128), conforming to standard IEEE 802.15.4 (LR-WPAN)  
 Power level: < 100 mW

#### ■ 5.4 Climate characteristics

Usage temperature: + 5° C to + 45° C  
 Storage temperature: 0° C to + 45°

## 6. CARE

Clean the surface with a cloth.  
Do not use acetone, tar-removing cleaning agents or trichloroethylene.

Resistant to the following products: Hexane (EN 60669-1), methylated spirit, soapy water, diluted ammonia, bleach diluted to 10%, window-cleaning products, pre-impregnated wipes.

**Caution:** Always test before using special cleaning products.

The plates must not be painted.



Take care to recycle the battery appropriately

## 7. ACCESSORIES

0 648 71: Repositionable adhesive for wireless control (x 4 supplied)

## 8. STANDARDS AND APPROVALS

The undersigned, LEGRAND, declares that the radio-electric equipment type (7 521 89 - 7 522 89 - 7 523 89) complies with directive 2014/53/EU. The full text of the EU declaration of conformity is available on the following website: [www.legrandoc.com](http://www.legrandoc.com)