


## Valena™ Life

## **Connected wireless control for roller shutters**

Cat. Nos: 7 521 91 - 7 522 91 - 7 523 91



## 1. USE

Zone or centralised control for wired roller shutter switches.


- Fixes directly on the wall or screws onto a flush-mounting box. Multi-gang versions can be combined with other wiring accessories.
- Fits on a piece of furniture (movable).

Can control up to 20 roller shutter switches.

## 2. RANGE


Description	White	Ivory	Aluminium
Connected wireless control for roller shutters. Supplied complete with battery. Equipped with an LED indicator (configuration) and a RESET button (hidden) used to return to factory settings. Repositionable self-adhesive fixings supplied.	7 521 91	7 522 91	7 523 91

## 3. DIMENSIONS (mm)



Cat. Nos	Α	В	D
7 521 91 - 7 522 91 - 7 523 91	86	86	12

## 4. OPERATION



#### 5. TECHNICAL CHARACTERISTICS

## ■ 5.1 Mechanical characteristics

Protection against impacts: IK 02 Protection against solid bodies/liquids:

- IP 20 without plate and rocker plate
- IP 40 for assembled product

## ■ 5.2 Material characteristics

Plate: ABS Sub-plate: PC Rocker plate: ABS

Mechanism with grid: Fibreglass-reinforced (10%) PC

Halogen-free UV resistant

Self-extinguishing: 650°C/30 s

## ■ 5.3 Electrical characteristics

Powered by a CR2032 - 3 V lithium battery (supplied)

Battery life: 8 years for 10 activations a day

ZigBee radio technology frequency: 2.4 GHz to 2.4835 GHz

Power level: < 100 mW

Wireless mesh network, self-adaptive and secure (AES 128), conforming to standard IEEE 802.15.4 (LR-WPAN)

## ■ 5.4 Climate characteristics

Usage temperature: + 5° C to + 45° C Storage temperature: 0° C to + 45° C

Fiche technique : F02605FR/00 Mise à jour : 05/09/2018 Créée : 27/02/2018

## Valena™ Life

# **Connected wireless control for roller shutters**

## 6. CARE

Clean the surface with a cloth.

Do not use acetone, tar-removing cleaning agents or trichloroethylene. Resistant to the following products: Hexane (EN 60669-1), methylated spirit, soapy water, diluted ammonia, bleach diluted to 10%, windowcleaning products, pre-impregnated wipes.

Caution: Always test before using special cleaning products.

The plates must not be painted.



Take care to recycle the battery appropriately

## 7. ACCESSORIES

0 648 71: Repositionable adhesive for wireless control (x 4 supplied)

## 8. STANDARDS AND APPROVALS

The undersigned, LEGRAND, declares that the radio-electric equipment type (7 521 91 - 7 522 91 - 7 523 91) complies with directive 2014/53/EU. The full text of the EU declaration of conformity is available on the  $following\ website: {\color{blue} www.legrandoc.com}$ 

2/2

Cat. Nos: 7 521 91 - 7 522 91 - 7 523 91